

WECO 957P Light Curtain Kit Power and Installation Hardware Included



The WECO 957P light curtain is an economical light curtain that can be installed universally **for both center opening and side opening doors, with or without nudging.**

Installation is fast and simple - it is designed to attach to either the door or the wall with equal ease and all the mounting hardware is included. The 957P's elements are quickly plugged into the 120VAC power supply (also included). The TX and RX cables are identical, making mis-plugging them impossible.

The units are 78.75 inches • 2 meters tall and **create a curtain using 94 crossbeams that work even in sunlight.**

These units comply with appropriate CE and cCSAus specifications.

Features

Works for both center opening and side slide doors

Meets CE and cCSAus standards

Power supply with and without nudging is included (unlike some competitors who sell them separately)

Easy to install - all hardware included

Cables are true traveling cables and are TX/RX interchangeable

Economical

In stock for quick delivery



WECO 957P Light Curtain Features

Feature	Description
Unit size	0.66 x 1.18 x 78.75 inches 17 x 30 x 2000 mm
Number of beams	94 non-parallel
Number of diodes	32 pairs
Scan mode	3 ways
Response time	65 ms
Diode spacing	2.3 inches • 59 mm
Operating height	up to 9.85 feet (13.12 feet as needed) up to 3 meters (4 meters as needed)
Detecting height	0.78 to 72.5 inches • 20 to 1841 mm
Infrared pulses ratio	1:2
Max. ambient light	≥ 100,000 lux
Linear tolerance	± 0.59 in. vertical, ± 0.16 in. horizontal ± 15 mm vertical, ± 4 mm horizontal
Connection cables	(2) 11.5 feet (2) 3.5 m
System indicators	Normal / Interrupted / Faulty
LED indicators	1 green, 1 red
Operating temp. range	-4 to 149°F • -20 to 65°C
Storage temp. range	-40 to 185°F • -40 to 85°C
IP rate	IP54
Isolation	≥ 1500V
Power unit	120VAC