

# TYPE APPROVAL CERTIFICATE

**This is to certify:**

**That the Electric Power Cable**

with type designation(s)  
**AFUMEX NAU XTCUA 0,6/1 kV,**  
**AFUMEX NAU XATA 0,6/1 kV,**  
**AFUMEX NAU-XOTCUA & AFUMEX NAU-XTCUA,**  
**EXZHELLENT MAR RO2Dt Cu5**

Issued to  
**PRYSMIAN CABLES SPAIN, S.A.**  
**Vilanova i la Geltrú, Barcelona, Spain**

is found to comply with  
**DNV GL rules for classification – Ships, offshore units, and high speed and light craft**

**Application :**

**General power and lighting. Control.**  
**Products approved by this certificate are accepted for installation on all vessels classed by DNV GL.**

Type	Rated voltage (kV)	Temp. class (°C)
<b>AFUMEX NAU XTCUA 0,6/1 kV</b>	<b>0,6/1</b>	<b>90</b>
<b>AFUMEX NAU XATA 0,6/1 kV</b>	<b>0,6/1</b>	<b>90</b>
<b>AFUMEX NAU-XOTCUA &amp; AFUMEX NAU-XTCUA</b>	<b>0,6/1</b>	<b>90</b>
<b>EXZHELLENT MAR RO2Dt Cu5</b>	<b>0,6/1</b>	<b>90</b>

Issued at **Høvik** on **2020-03-17**

for **DNV GL**

This Certificate is valid until **2023-06-30**.

DNV GL local station: **Barcelona FIS**

Approval Engineer: **Ivar Bull**

**Marta Alonso Pontes**  
**Head of Section**

This Certificate is subject to terms and conditions overleaf. Any significant change in design or construction may render this Certificate invalid. The validity date relates to the Type Approval Certificate and not to the approval of equipment/systems installed.



Job Id: **262.1-015325-13**  
 Certificate No: **TAE00002ZA**  
 Revision No: **1**

## Product description

Type: AFUMEX NAU XTCUA 0,6/1 kV 0,6/1  
 AFUMEX NAU XATA 0,6/1 kV 0,6/1  
 AFUMEX NAU-XOTCUA & AFUMEX NAU-XTCUA 0,6/1  
 EXZHELLENT MAR RO2Dt Cu5 0,6/1

### Construction:

Conductors: Plain or tinned, stranded copper. Class 2 or class 5  
 Core insulation: HF XLPE  
 Filler: Tape or Halogen free compound (if necessary)  
 Metallic Screen: Helically copper tape overlapped (XOTCUA))  
 Metal covering: Plain or tinned copper wire braid (TCU) or  
 Galv. steel wire braid (T) (Not for single core cables)  
 Outer sheath: SHF1

No of cores:	Cross sectional area [mm <sup>2</sup> ]
1	1 - 300
2, 4	1 - 120
3	1 - 185
5	4 - 120
5, 7, 10, 12, 14, 16, 19, 20, 24, 27, 30, 37	1,5 2,5

AFUMEX NAU-XOTCUA & AFUMEX NAU-XTCUA 0,6/1 kV

Number of cores	Conductor cross section [mm <sup>2</sup> ]
3G	2.5, 4, 6, 10

## Application/Limitation

The requirements of SOLAS Amendments Chapter II-1, Part D, Reg. 45, 5.2 (provision to be taken to limit Fire Propagation along Bunches of Cables or Wires) are fulfilled without any additional measures.

## Type Approval documentation

[Data sheets](#)  
[Test reports](#)

## Tests carried out

	Release	General description	Limitation
DNVGL-CP-0399	2016-03	Class Programme Electric cables	
IEC 60092-350	2014-08	General construction and test methods of power, control and instrumentation cables for shipboard and offshore applications	
IEC 60092-360	2014-04	Electrical installations in ships - Part 360: Insulating and sheathing materials for shipboard and offshore units, power, control, instrumentation and telecommunication cables.	
IEC 60092-353	2016-09	Electrical installations in ships - Part 353: Power cables for rated voltages 1 kV and 3 kV	
IEC 60332-1-2	2006-07	Tests on electric cables under fire conditions. Test for vertical flame propagation for a single insulated wire or cable.	

Job Id: **262.1-015325-13**  
Certificate No: **TAE00002ZA**  
Revision No: **1**

	<b>Release</b>	<b>General description</b>	<b>Limitation</b>
DNVGL-CP-0399	2016-03	Class Programme Electric cables	
IEC 60332-3-22	2018-07	Tests on electric cables under fire conditions - Part 3-22: Test for vertical flame spread of vertically-mounted bunched wires or cables - Category A	Charred portion of sample does not exceed 2,5m above bottom edge of burner.
IEC 60754-1	2011-11	Test on gases evolved during combustion of materials from cables - Part 1: Determination of the halogen acid gas content	Low Halogen: <0,5% Halogen
IEC 60754-2	2011-11	Test on gases evolved during combustion of materials from cables - Part 2: Determination of acidity (by pH measurement) and conductivity	Halogen free: pH > 4,3 Conductivity < 10µS/mm
IEC 61034-1/2	2013-07 2013-09	Measurement of smoke density of cables burning under defined conditions – Test apparatus, procedure and requirements	Low smoke Light transmittance $\geq 60\%$

### Marking of product

PRYSMIAN SAP - AFUMEX NAU XTCUA or XATA or XOTCUA or XTCUA - size - 0,6/1 kV – IEC 60332-3A - Lot No. or

GENERAL CABLE SAP - EXZHELLENT MAR RO2Dt Cu5 - size - 0,6/1 kV – IEC 60332-3/A - Lot No.

SAP = Santa Perpetua Plant.

### Periodical assessment

The scope of the periodical assessment is to verify that the conditions stipulated for the Type approval are complied with and that no alterations are made to the product design or choice of materials.

The main elements of the assessment are:

- Inspection on factory samples, selected at random from the production line (where practicable)
- Results from Routine tests (RT) and selected type tests (ref. to applicable class programs) checked (if not available these tests shall be carried out)
- Review of type approval documentation
- Review of possible change in design, materials and performance
- Ensuring traceability between manufacturer's product type marking and Type Approval Certificate.

Periodical assessment is to be performed after 2 years and after 3.5 years. A renewal assessment will be performed at renewal of the certificate.

END OF CERTIFICATE