

TYPE APPROVAL CERTIFICATE**This is to certify:****That the High Voltage Cable**

with type designation(s)

TEOF or Exzhellent 606 RFOU (P2) & TEOF or Exzhellent 606 RFOU (P2/P9) 3,6/6 kV, TEOF or Exzhellent 606 RFOU (P3) & TEOF or Exzhellent 606 RFOU (P3/P10) 6/10 kV, TEOF or Exzhellent 606 RFOU (P4) & TEOF or Exzhellent 606 RFOU (P4/P11) 8,7/15 kV, TEOF or Exzhellent 606 RFOU (P19) & TEOF or Exzhellent 606 RFOU (P19/P21) 12/20 kV

Issued to

PRYSMIAN CABLES SPAIN, S.A.
Vilanova i la Geltrú, Barcelona, Spain

is found to comply with

DNV GL rules for classification – Ships, offshore units, and high speed and light craft**Application :****General power.****Products approved by this certificate are accepted for installation on all vessels classed by DNV GL.**

Type	Rated voltage (kV)	Temp. class (°C)
TEOF or Exzhellent 606 RFOU (P2) & TEOF or Exzhellent 606 RFOU (P2/P9) 3,6/6 kV	3,6/6	90
TEOF or Exzhellent 606 RFOU (P3) & TEOF or Exzhellent 606 RFOU (P3/P10) 6/10 kV	6/10	90
TEOF or Exzhellent 606 RFOU (P4) & TEOF or Exzhellent 606 RFOU (P4/P11) 8,7/15 kV	8,7/15	90
TEOF or Exzhellent 606 RFOU (P19) & TEOF or Exzhellent 606 RFOU (P19/P21) 12/20 kV	12/20	90

Issued at **Høvik** on **2019-12-04**for **DNV GL**This Certificate is valid until **2023-06-30**.DNV GL local station: **Barcelona**Approval Engineer: **Ivar Bull****Trond Sjøvåg**
Head of Section

This Certificate is subject to terms and conditions overleaf. Any significant change in design or construction may render this Certificate invalid. The validity date relates to the Type Approval Certificate and not to the approval of equipment/systems installed.



Product description

TEOF or Exzhellent 606 RFOU (P2) & TEOF or Exzhellent 606 RFOU (P2/P9) 3,6/6 kV,
 TEOF or Exzhellent 606 RFOU (P3) & TEOF or Exzhellent 606 RFOU (P3/P10) 6/10 kV,
 TEOF or Exzhellent 606 RFOU (P4) & TEOF or Exzhellent 606 RFOU (P4/P11) 8,7/15 kV,
 TEOF or Exzhellent 606 RFOU (P19) & TEOF or Exzhellent 606 RFOU (P19/P21) 12/20 kV

Construction:
 Conductors: Tinned annealed, stranded copper Class 2 or Class 5
 Core insulation: EPR
 Inner sheath: SHF2
 Metal covering: Tinned copper wire braid
 Outer sheath: SHF2 or SHF Mud

Single cores

Voltage U0 / U [kV]				
3,6/6	6/10	8,7/15	12/20	18/30
RFOU P2/9	RFOU P3/P10	RFOU P4/P11	RFOU P19/21	-
-	-	-	-	-
1 x 25	1 x 25	1 x 25	-	-
1 x 35	1 x 35	1 x 35	1 x 35	-
1 x 50	1 x 50	1 x 50	1 x 50	-
1 x 70	1 x 70	1 x 70	1 x 70	-
1 x 95	1 x 95	1 x 95	1 x 95	-
1 x 120	1 x 120	1 x 120	1 x 120	-
1 x 150	1 x 150	1 x 150	1 x 150	-
1 x 185	1 x 185	1 x 185	1 x 185	-
1 x 240	1 x 240	1 x 240	1 x 240	-
1 x 300	1 x 300	1 x 300	1 x 300	-

3 cores

Voltage U0 / U [kV]				
3,6/6	6/10	8,7/15	12/20	18/30
RFOU P2/9	RFOU P3/P10	RFOU P4/P11	RFOU P19/21	-
-	-	-	-	-
-	-	-	-	-
3 x 25	3 x 25	3 x 25	-	-
3 x 35	3 x 35	3 x 35	3 x 35	-
3 x 50	3 x 50	3 x 50	3 x 50	-
3 x 70	3 x 70	3 x 70	3 x 70	-
3 x 95	3 x 95	3 x 95	3 x 95	-
3 x 120	3 x 120	3 x 120	3 x 120	-
3 x 150	3 x 150	3 x 150	3 x 150	-
3 x 185	3 x 185	3 x 185	3 x 185	-
3 x 240	3 x 240	3 x 240	3 x 240	-
3 x 300	3 x 300	3 x 300	3 x 300	-

Application/Limitation

The requirements of SOLAS Amendments Chapter II-1, Part D, Reg. 45, 5.2 (provision to be taken to limit Fire Propagation along Bunches of Cables or Wires) are fulfilled without any additional measures.

Type Approval documentation

Data sheets: TEOF RFOU - TEOF RFOU 3,6/6 kV
 TEOF RFOU - TEOF RFOU 6/10 kV
 TEOF RFOU - TEOF RFOU 8,7/15 kV rev. 00 dated 05/11.
 TEOF RFOU - TEOF RFOU 12/20 kV rev. 00 dated 05/11.

Test report dated 17.05.1996

Tests carried out

	Release	General description	Limitation
DNVGL-CP-0399	2016-03	Class Programme Electric cables	
IEC 60092-350	2014-08	General construction and test methods of power, control and instrumentation cables for shipboard and offshore applications	
IEC 60092-360	2014-04	Electrical installations in ships - Part 360: Insulating and sheathing materials for shipboard and offshore units, power, control, instrumentation and telecommunication cables.	
IEC 60092-354	2014-08	Electrical installations in ships - Part 354: Single- and three-core power cables with extruded solid insulation for rated voltages 6 kV (Um = 7,2 kV) up to 30 kV (Um = 36 kV)	
IEC 60332-1-2	2006-07	Tests on electric cables under fire conditions. Test for vertical flame propagation for a single insulated wire or cable.	
IEC 60332-3-22	2018-07	Tests on electric cables under fire conditions - Part 3-22: Test for vertical flame spread of vertically-mounted bunched wires or cables - Category A	Charred portion of sample does not exceed 2,5m above bottom edge of burner.
IEC 60754-1	2011-11	Test on gases evolved during combustion of materials from cables - Part 1: Determination of the halogen acid gas content	Low Halogen: <0,5% Halogen
IEC 60754-2	2011-11	Test on gases evolved during combustion of materials from cables - Part 2: Determination of acidity (by pH measurement) and conductivity	Halogen free: pH > 4,3 Conductivity < 10µS/mm
IEC 61034-1/2	2013-07 2013-09	Measurement of smoke density of cables burning under defined conditions – Test apparatus, procedure and requirements	Low smoke Light transmittance ≥60%
NEK 606 Ed. 4	2009-05	Cables for offshore installations. Halogen-free and/or mud resistant. Technical specification.	

Job Id: **262.1-015325-7**
Certificate No: **TAE00002ZG**

Marking of product

PRYSMIAN SAP –

TEOF or Exzhellent 606 RFOU (P2) & TEOF or Exzhellent 606 RFOU (P2/P9) 3,6/6 kV,
TEOF or Exzhellent 606 RFOU (P3) & TEOF or Exzhellent 606 RFOU (P3/P10) 6/10 kV,
TEOF or Exzhellent 606 RFOU (P4) & TEOF or Exzhellent 606 RFOU (P4/P11) 8,7/15 kV,
TEOF or Exzhellent 606 RFOU (P19) & TEOF or Exzhellent 606 RFOU (P19/P21) 12/20 kV
- size – IEC 60332-3-22 - Lot No.

Periodical assessment

The scope of the periodical assessment is to verify that the conditions stipulated for the Type approval are complied with and that no alterations are made to the product design or choice of materials.

The main elements of the assessment are:

- Inspection on factory samples, selected at random from the production line (where practicable)
- Results from Routine tests (RT) and selected type tests (ref. to applicable class programs) checked (if not available these tests shall be carried out)
- Review of type approval documentation
- Review of possible change in design, materials and performance
- Ensuring traceability between manufacturer's product type marking and Type Approval Certificate.

Periodical assessment is to be performed after 2 years and after 3.5 years. A renewal assessment will be performed at renewal of the certificate.

END OF CERTIFICATE